



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LT212 2-1/2" Met L/T, Non UI 25' *Southwire Company*

Catalog Number	LT212
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 2-1/2 In Trade Size, 2.84 to 2.875 In Conduit Outer Diameter, 2.48 to 2.505 In Conduit Inner Diameter, Titan(R) Ef Style, 25 FT Length, Galvanized, Gray, 15 In Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 156 LB/100 FT
Weight per unit	1.4 (lbs/ft)
Product Category	Liquid Tight Conduit

Features

outside diameter	2757
------------------	------

Dimensions and Weight

Diameter	2-1/2"
----------	--------

Descriptions

Description	2-1/2" MET L/T, NON UL 25'
extra long description	SWC 55107301 Titan2 Type EF Extra-F

Manufacturer Information

GTIN	00032886043123
UPC	032886043123

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Packaging

Carton	25
Weight Per foot	1.37