



Product Quick Search

[HOME](#) | [WHERE TO BUY](#) | [CONTACT US](#) | [SITE MAP](#)

- PRODUCTS
- SUPPORT
- NEWS/EVENTS
- ABOUT BALDOR
- INVESTOR RELATIONS

General Information

- [Overview](#)
- [Specifications](#)
- [Performance Data](#)
- [Parts List](#)
- [Dimensional Dwg](#)
- [Connection Diag](#)
- [Product Literature](#)
- More Information**
- [Locate Distributor](#)
- [Baldor Sales Offices](#)

[Return to List](#)

[AC Controls](#) | [Inverter_GeneralPurpose](#) |

Specifications: ID15H403-E

Catalog Number:	ID15H403-E
Specification Number:	IN0828A00
Horsepower/Kilowatt:	3/2.2
Input Voltage/Hertz:	50/60
Input Phase Rated:	3
Output Frequency - Maximum:	400
Enclosure:	NEMA 1
Cooling Type:	FORCED AIR
Ambient Temperature Minimum:	0
Ambient Temperature Maximum:	40
Control Type:	Inverter - General Purpose
Number of Axis:	1
Operator Interface:	KEYPAD
Dynamic/Regenerative Braking:	DYNAMIC
DC Injunction Braking:	Y

Agency Approvals

UL:	Approved
CUL:	Approved
CE:	N/A
IEEE519:	N/A

Installed Options

RS232:	Optional
RS422/RS485:	Optional
Pneumatic-In/Relay-Out:	Optional
Isolated Input:	Optional
Master/Pulse/Follower:	Optional
DC Tach Interface:	Optional
Hi-Res Analog Input:	Optional
Isolated Encoder:	N/A
Resolver Input:	N/A

Analog Relay Output:	Optional
Macro:	N/A
Dimensions:	12"h x 7.7"w x 7.1"d

* For certified information, contact your local [Baldor office](#).

[Products](#) | [Support](#) | [News/Events](#) | [About Baldor](#) | [Investor Relations](#) | [Home](#)

Baldor Electric Company is an equal opportunity employer.

Copyright © 2001-2007 Baldor Electric Company. All rights reserved.

This site works best with Internet Explorer and Netscape 4.x and above.