

Fluorescent lampholders

Fluorescent lampholders

Product description

Recessed double contact 660W, 600V/AC

Features

- as well as enclosed outdoor signs
- for flush or surface mounting
- · Captive pal nut for easy mounting
- · Push-in wire terminals feature release slots
- Molded of durable white thermoset plastic

1.12" (28.4mm) 1.17" (29.7mm) 0.59" (15.0mm) 2.31" (58.7mm) 1.44" (36.6mm)

1.45" (36.8mm)

2503W

2500W

- · For replacement use in fluorescent lighting fixtures
- Recessed double-contact lampholders can be used

Commercial grade receptacles





Katıng					
W	V/AC	Description	Color	Catalog no.	RoHS
660	600	Plunger, push wire cap, screw switch	W	□ 2501W	•
		Stationary, push wire cap, screw switch	W	□ 2500W	•

For panel cutout dimensional data, see Section Q-Technical Reference

Fluorescent lampholders

Product description

Slimline

660W, 600V/AC; 660W, 1000V/AC

- For replacement use in fluorescent lighting fixtures as well as enclosed outdoor signs
- Plunger lampholders feature non-sticking, spring-loaded plunger to hold lamp securely
- · Captive pal nut for easy mounting
- · Push-in wire terminals feature release slots



2504W



2506W



Slimline fluorescent lampholders



Rating					
W	V/AC	Description	Color	Catalog no.	RoHS
660	600	Stationary, push wire cap, slide-on switch	W	□ 2506W	•
		Stationary, push wire cap, screw switch	W	□ 2503W	
660	1000	Plunger, push wire cap, slide-on switch	W	□ 2507W	•
		Plunger, push wire cap, screw switch	W	□ 2504W	

For panel cutout dimensional data, see Section Q-Technical Reference

Color information:

W (White)



Compliances, specifications and availability are subject to change without notice.