



Job Name:

Job Type:

Comments:

Quantity:

31191-07: Five-Light Serenity Chandelier



Dimensions:

Diameter: 29"

Overall Height: 59"

Height: 22 1/2"

Wire: 144" (color/Black)

Chain: 36"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulbs:

- 5 - Medium A19 100w Max. 120v - Not included
- 5 - LED Medium A19 8w Max. 120v - Not included
- 5 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps

Material List:

- 1 Body - Steel - Weathered Iron
- 1 Chain - Steel - Weathered Iron

Safety Listing:

- UL Listed for Dry Locations
- cUL Listed for Dry Locations

Instruction Sheets:

- English (HC-830)
- French (F-004)

Collection: Serenity

Five Light Chandelier in Weathered Iron Finish with Dusted Alabaster Glass Shades.

A soft, contemporary design in weathered iron finish with dusted alabaster glass.

Ref: 39059BLE

UPC #:785652119101

Finish: Weathered Iron (07)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Dusted Alabaster	5					8 1/2				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			1 1/8	5 5/16		

Replacement Bulb Data:

Product #		Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted	A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted	A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted	A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted	A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
--------------	-----------	----------	-----	--------	-------	--------	------	--------	-----------	----------

Individual	31191-07	1	785652119101	26.5	13	20.25	4.037	20.1	150	Yes
NJ Pallet		20		48	40	73	81.111	409		No
NV Pallet		20		48	40	77	85.556	402		No



Job Name:

Job Type:

Comments:

Quantity:

31191-07: Five-Light Serenity Chandelier



Dimensions:

Diameter: 29"
Height: 22 1/2"

Overall Height: 59"
Wire: 144" (color/Black)
Chain: 36"
Mounting Proc.: Center Lock-Up
Connection: Mounted To Box

Bulbs:

5 - Medium A19 100w Max. 120v - Not included
5 - LED Medium A19 8w Max. 120v - Not included
5 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps

Material List:

1 Body - Steel - Weathered Iron
1 Chain - Steel - Weathered Iron

Safety Listing:

UL Listed for Dry Locations
cUL Listed for Dry Locations

Instruction Sheets:

English (HC-830)
French (F-004)

Collection: Serenity

Five Light Chandelier in Weathered Iron Finish with Dusted Alabaster Glass Shades.

A soft, contemporary design in weathered iron finish with dusted alabaster glass.

Ref: 39059BLE

UPC #:785652119101

Finish: Weathered Iron (07)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Dusted Alabaster	5					8 1/2				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			1 1/8	5 5/16		

Replacement Bulb Data:

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted	A19	8	8	120v	50000	450	3000	85
97408S	Frosted	A19	8	8	120v	50000	450	2700	85
97309S	Frosted	A19	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted	A19	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
--------------	-----------	----------	-----	--------	-------	--------	------	--------	-----------	----------

Individual	31191-07	1	785652119101	26.5	13	20.25	4.037	20.1	150	Yes
NJ Pallet		20		48	40	73	81.111	409		No
NV Pallet		20		48	40	77	85.556	402		No