



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



62MAX IP54 Ir Thermometer *Fluke Electronics*

| | |
|------------------|---|
| Catalog Number | 62MAX |
| Manufacturer | Fluke Electronics |
| Description | The Fluke 62 Max Infrared Thermometers Are Everything You'D Expect From The Experts In Measuring Temperature In Transformers, Motors, Pumps, Panels, Breakers, Compressors, Duct, Steam Lines, Valves, and Vents In Hard to Reach Areas For Repair and Maintenance. Small In Size, Extremely Accurate and Yet Easy to Use . IP54 Rated For Dust and Water Resistance. Precise Yet Rugged Enough to Take A 3-Meter Drop. |
| Weight per unit | 1.3 (lbs/each) |
| Product Category | Meters, Panel Instruments |

Features

| | |
|-------------------|---|
| Response Time | 500m |
| Temperature Range | -30 ?°C to 500 ?°C (-22 ?°F to 932 ?°F) |

Descriptions

| | |
|------------------------|---|
| Description | IP54 IR THERMOMETER |
| extra long description | FLK FLUKE-62-MAX IP54 IR THRMTR |
| Long Description | The Fluke 62 MAX infrared thermometers are everything you'd expect from the experts in measuring temperature in transformers, motors, pumps, panels, breakers, compressors, duct, steam lines, valves, and vents in hard to reach areas for repair and maintenance. Small in size, extremely accurate and yet easy to use . IP54 rated for dust and water resistance. Precise yet rugged enough to take a 3-meter drop. |
| Product Type | IP54 Ir THRMTR |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | FLUKE |
| GTIN | 00095969620208 |
| Manufacturers Part Number | FLUKE-62-MAX |
| UPC | 095969620208 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | TEST EQUIPMENT, TESTERS AND MULTIMETERS |
|----------------------|---|

Packaging

| | |
|-----------------|------|
| Carton | 3 |
| Weight Per each | 1.28 |