



Fluorescent Lamps

Bulb Base	Nominal Length Order			Description	Case Qty.	Rated Life		Lumens		Color Temp.		Foot- notes	Warning and Cautions		Additional Information
	Watts	in.	Code			3hr/ Start	12hr/ Start	Initial	Mean	K	CRI				
T5 STARCOAT ECOLUX® LAMPS															
HIGH EFFICIENCY															
T5 Miniature BiPin (G5)	14	21.6	31590	F14W/T5/830/ECO	40	30000	36000	1350	1240	3000	85	19	101		
			46671	F14W/T5/835/ECO	40	30000	36000	1350	1240	3500	85	19	101		
			46673	F14W/T5/841/ECO	40	30000	36000	1350	1240	4100	85	19	101		
			46674	F14W/T5/850/ECO	40	30000	36000	1300	1190	5000	85	19	101		
			46676	F14W/T5/865/ECO	40	30000	36000	1250	1150	6500	85	19	101		
	21	33.4	46677	F21W/T5/830/ECO	40	30000	36000	2100	1930	3000	85	19	101		
			46684	F21W/T5/835/ECO	40	30000	36000	2100	1930	3500	85	19	101		
			46687	F21W/T5/841/ECO	40	30000	36000	2100	1930	4100	85	19	101		
			46688	F21W/T5/850/ECO	40	30000	36000	2000	1840	5000	85	19	101		
			46689	F21W/T5/865/ECO	40	30000	36000	1950	1790	6500	85	19	101		
	28	45.2	46704	F28W/T5/830/ECO	40	30000	36000	2900	2660	3000	85	19	101		
			46705	F28W/T5/835/ECO	40	30000	36000	2900	2660	3500	85	19	101		
			46706	F28W/T5/841/ECO	40	30000	36000	2900	2660	4100	85	19	101		
			46707	F28W/T5/850/ECO	40	30000	36000	2750	2530	5000	85	19	101		
			46708	F28W/T5/865/ECO	40	30000	36000	2700	2480	6500	85	19	101		
	35	57.1	46724	F35W/T5/830/ECO	40	30000	36000	3650	3350	3000	85	19	101		
			46727	F35W/T5/835/ECO	40	30000	36000	3650	3350	3500	85	19	101		
			46735	F35W/T5/841/ECO	40	30000	36000	3650	3350	4100	85	19	101		
			46742	F35W/T5/850/ECO	40	30000	36000	3500	3220	5000	85	19	101		
			46743	F35W/T5/865/ECO	40	30000	36000	3400	3120	6500	85	19	101		
HIGH OUTPUT															
T5 Miniature BiPin (G5)	24	21.6	46699	F24W/T5/830/ECO	40	30000	36000	2000	1840	3000	85	19	101		
			46700	F24W/T5/835/ECO	40	30000	36000	2000	1840	3500	85	19	101		
			46701	F24W/T5/841/ECO	40	30000	36000	2000	1840	4100	85	19	101		
			46702	F24W/T5/850/ECO	40	30000	36000	1900	1740	5000	85	19	101		
			46703	F24W/T5/865/ECO	40	30000	36000	1900	1740	6500	85	19	101		
	39	33.4	46744	F39W/T5/830/ECO	40	30000	36000	3500	3220	3000	85	19	101		
			46745	F39W/T5/835/ECO	40	30000	36000	3500	3220	3500	85	19	101		
			46746	F39W/T5/841/ECO	40	30000	36000	3500	3220	4100	85	19	101		
			46747	F39W/T5/850/ECO	40	30000	36000	3350	3080	5000	85	19	101		
			46748	F39W/T5/865/ECO	40	30000	36000	3330	3060	6500	85	19	101		
	54	45.2	46759	F54W/T5/830/ECO	40	30000	36000	5000	4600	3000	85	19	101		
			46760	F54W/T5/835/ECO	40	30000	36000	5000	4600	3500	85	19	101		
			46761	F54W/T5/841/ECO	40	30000	36000	5000	4600	4100	85	19	101		
			46762	F54W/T5/850/ECO	40	30000	36000	4800	4410	5000	85	19	101		
			46763	F54W/T5/865/ECO	40	30000	36000	4750	4370	6500	85	19	101		
	49	57.1	46751	F49W/T5/830/ECO	40	30000	36000	4900	4500	3000	85	19	101		
			46752	F49W/T5/835/ECO	40	30000	36000	4900	4500	3500	85	19	101		
			46753	F49W/T5/841/ECO	40	30000	36000	4900	4500	4100	85	19	101		
			46757	F49W/T5/850/ECO	40	30000	36000	4700	4320	5000	85	19	101		
			46758	F49W/T5/865/ECO	40	30000	36000	4650	4270	6500	85	19	101		
	80	57.1	46802	F80W/T5/830/ECO	40	30000	36000	7000	6440	3000	85	19	101		
			46803	F80W/T5/835/ECO	40	30000	36000	7000	6440	3500	85	19	101		
			46804	F80W/T5/841/ECO	40	30000	36000	7000	6440	4100	85	19	101		
			46805	F80W/T5/850/ECO	40	30000	36000	6700	6160	5000	85	19	101		
			46806	F80W/T5/865/ECO	40	30000	36000	6650	6110	6500	85	19	101		