

# FIBERGLASS

**300** lbs. **TYPE IA**  
load capacity\*  
\*includes weight of worker and tools

## STEPLADDER FS1500 SERIES



- Da Boot™ Patent #7,000,731 B2
- Molded Top with Tool Slots
- Inside spreader braces
- Double-rivet step construction
- Wide Back Braces
- Full channel fiberglass rail



MODEL	SIZE	STEP SIZE	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WT. (LBS)	APPROX. CUBES
FS1502*	2'	3"	17"	18 1/4"	8	2.07'
FS1503	3'	3"	18 7/8"	28"	12	3.18'
FS1504	4'	3"	199/16"	2815/16"	14	3.18'
FS1505	5'	3"	211/16"	34 7/8"	17	4.27'
FS1506	6'	3"	229/16"	40 7/8"	20	5.49'
FS1508	8'	3"	259/16"	52 3/4"	26	8.29'
FS1510	10'	3"	289/16"	6411/16"	34	11.67'
FS1512	12'	3"	319/16"	76 1/16"	47	15.49'

\*FS1502 is a folding step stand and is not equipped with Da Boot™

# FIBERGLASS

**250** lbs. **TYPE I**  
load capacity\*  
\*includes weight of user and tools

## STEPLADDER FS2000 SERIES



- Slip resistant rubber feet
- Molded Top with Handyman's Tool Slots
- Pinch resistant spreader braces
- Double-rivet step construction
- Optional Molded Pail Shelf



MODEL	SIZE	STEP SIZE	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WT. (LBS)	APPROX. CUBES
FS2004	4'	3"	18 13/16"	28 3/16"	12	3.18'
FS2005	5'	3"	20 5/16"	34 1/8"	15	4.27'
FS2006	6'	3"	21 13/16"	40"	17	5.49'
FS2008	8'	3"	24 13/16"	51 7/8"	22	8.29'

# FIBERGLASS

**225** lbs. **TYPE II**  
load capacity\*  
\*includes weight of user and tools

## STEPLADDER FS4000 SERIES



- Molded Top with Tool Slots
- Slip resistant Feet
- Pinch resistant spreader braces
- Fiberglass rails



MODEL	SIZE	BASE WIDTH	SPREAD	APPROX. WT. (LBS)	APPROX. CUBES
FS4004	4'	18 3/16"	283/16"	11	2.7'
FS4006	6'	21 13/16"	401/16"	16	4.4'
FS4007	7'	23 5/16"	46"	18	5.3'
FS4008	8'	24 13/16"	51 7/8"	21	6.2'

# FIBERGLASS

**300** lbs. **TYPE IA**  
load capacity\*

## STEPLADDER FS1500 SERIES



- Da Boot™ Patent #7,000,731 B2
- Molded Top with Tool Slots
- Inside spreader braces
- Double-rivet step construction
- Wide Back Braces
- Full channel fiberglass rail



MODEL	SIZE	STEP SIZE	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WT. (LBS)	APPROX. CUBES
FS1502*	2'	3"	17"	18 1/4"	8	2.07'
FS1503	3'	3"	18 7/8"	28"	12	3.18'
FS1504	4'	3"	199/16"	2815/16"	14	3.18'
FS1505	5'	3"	211/16"	34 7/8"	17	4.27'
FS1506	6'	3"	229/16"	40 7/8"	20	5.49'
FS1508	8'	3"	259/16"	52 3/4"	26	8.29'
FS1510	10'	3"	289/16"	6411/16"	34	11.67'
FS1512	12'	3"	319/16"	76 1/16"	47	15.49'

\*FS1502 is a folding step stand and is not equipped with Da Boot™

# FIBERGLASS

**250** lbs. **TYPE I**  
load capacity\*

## STEPLADDER FS2000 SERIES

- Slip resistant rubber feet
- Molded Top with Handyman's Tool Slots
- Pinch resistant spreader braces
- Double-rivet step construction
- Optional Molded Pail Shelf



MODEL	SIZE	STEP SIZE	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WT. (LBS)	APPROX. CUBES
FS2004	4'	3"	18 13/16"	28 3/16"	12	3.18'
FS2005	5'	3"	20 5/16"	34 1/8"	15	4.27'
FS2006	6'	3"	21 13/16"	40"	17	5.49'
FS2008	8'	3"	24 13/16"	51 7/8"	22	8.29'

# FIBERGLASS

**225** lbs. **TYPE II**  
load capacity\*

## STEPLADDER FS4000 SERIES

- Molded Top with Tool Slots
- Slip resistant Feet
- Pinch resistant spreader braces
- Fiberglass rails



MODEL	SIZE	BASE WIDTH	SPREAD	APPROX. WT. (LBS)	APPROX. CUBES
FS4004	4'	18 3/16"	283/16"	11	2.7'
FS4006	6'	21 13/16"	401/16"	16	4.4'
FS4007	7'	23 5/16"	46"	18	5.3'
FS4008	8'	24 13/16"	51 7/8"	21	6.2'