

## Pro-Stock Panelboard, Unassembled A-Series Lighting Panels

### Select Main and/or Sub-feed Breaker Kit

Select main breaker kit appropriate for your interior type (see Step 1), for your amp rating and for the necessary kAIC rating. Enter the product number in Row 4A of the Pro-Stock Selector along with the corresponding price. If a sub-feed breaker is also required, repeat the selection process and complete Row 4B in the Pro-Stock Selector. **Note: 400A and 600A breaker kits cannot be used for sub-feed applications.** For additional details and pricing, see Section 4 of the BuyLog.

Interior Type	Product Number <sup>1</sup>	List Price, GO-101P	Max Amp	No. of Poles	Breaker Rating (kAIC)							
					10	14	22	25	65	100	200	
AQU1: 240 VAC, 1 Phase	MB612	\$35.00	100	2	THQB		THHQB					
	MB614	\$80.00	100	4	(2) THQB		(2) THHQB					
	MB512	\$118.00	225	2	TQD		THQD					
	MB712	\$140.00	400	2			TJD					
	MB332	\$145.00	400	2					SGHA	SGLA	SGPA	
	MB332	\$145.00	600	2					SGHA	SGLA	SGPA	
	MB332WB	\$4225.00	600	2					SGHA+Kit			
AQU3: 208/120 VAC, 3 Phase	MB613	\$35.00	100	3	THQB		THHQB					
	MB616	\$90.00	100	6	(2) THQB		(2) THHQB					
	MB513	\$92.00	225	3	TQD		THQD					
	MB516	\$210.00	225	6	(2) TQD		(2) THQD					
	MB233	\$125.00	225	3					SFHA	SFLA	SFPA	
	MB233WB	\$1325.00	225	3					SFHA+Kit			
	MB2332 <sup>5</sup>	\$125.00	225	6 <sup>5</sup>					2nd SFHA			
	MB2332WB <sup>5</sup>	\$1500.00	225	6 <sup>5</sup>					2nd SFHA+Kit			
	MB713	\$135.00	400	3			TJD					
	MB333	\$160.00	400	3					SGHA	SGLA	SGPA	
	MB333	\$160.00	600	3					SGHA	SGLA	SGPA	
MB333WB	\$5100.00	600	3					SGHA+Kit				
AEU3: 480/277 Vac, 3 Phase	MB423	\$35.00	100	3		TEY						
	MB426	\$90.00	100	6		(2) TEY						
	MB133	\$52.00	150	3		TED <sup>2</sup>		THED				
	MB133	\$52.00	150	3				SEHA	SELA	SEPA		
	MB133WB	\$1000.00	150	3				SEHA+Kit				
	MB233	\$125.00	225	3				SFHA <sup>4</sup>	SFLA	SFPA		
	MB233WB	\$1325.00	225	3				SFHA+Kit <sup>4</sup>				
	MB2332 <sup>5</sup>	\$125.00	225	6 <sup>5</sup>				2nd SFHA <sup>4</sup>				
	MB2332WB <sup>5</sup>	\$1500.00	225	6 <sup>5</sup>				2nd SFHA+Kit <sup>4</sup>				
	MB823	\$80.00	400	3				TJJ <sup>3</sup>				
	MB333	\$160.00	400	3				SGHA <sup>4</sup>	SGLA	SGPA		
MB333	\$160.00	600	3				SGHA <sup>4</sup>	SGLA	SGPA			
MB333WB	\$5100.00	600	3				SGHA+Kit <sup>4</sup>					

<sup>1</sup> Breaker not included except for "WB" kits (where product number ends in "WB"). "WB"s include Spectra breaker, Spectra kit and lugs. Rating plugs must be ordered separately.

<sup>2</sup> Actual breaker rating is 18kAIC.

<sup>3</sup> Actual breaker rating is 30kAIC.

<sup>4</sup> Actual breaker rating is 35kAIC.

<sup>5</sup> To achieve 6 poles of subfeed, the MB233WB or MB233 kit is also required. 6 poles of subfeed only work with 400A and 600A interiors.

