



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS60SSAX 60A 600VAC N/F Safety Switch W/Aux.

Pass & Seymour/Legrand

Catalog Number	PS60SSAX
Manufacturer	Pass & Seymour/Legrand
Description	Non-Fusible Safety Switch With Auxillary Contact. 60 Amp, 600 Vac.
Weight per unit	4.4 (lbs/each)
Product Category	Non-Fusible Disconnect Safety

Features

action	Motor Disconnect Switch
amperage rating	60
connection	Hard Wired
Contact Configuration	1 N.O. & 1 N.C.
Contact Rating	10A @ 600VAC
insulation	Complies with NEMA 4X
Material	Valox 357®
operating cycles	Electrical: 10,000 Cycles;Mechanical: 15,000 Cycles
Poles	4
Switch Type	Switch Handle
Voltage Rating	600

Dimensions and Weight

Height	12.38
Width	6.31

Descriptions

Description	60A 600VAC N/F SAFETY SWITCH W/AUX.
extra long description	P&S PS60SSAX 60A 600VAC N/F SAFETY
Long Description	Non-Fusible Safety Switch with Auxillary Contact. 60 amp, 600 vac.
Product Type	60A 600VAC N/F Safety Switch W/Aux.
Special Features	Compact design fits in most I-beams to provide mounting versatility, easy access, and reduced possibility of impact damage. Nonconductive, watertight, corrosion-, heat-, and impact-resistant Valox® enclosure ensures NEMA 4X and 12 ratings and withstands the harshest industrial environments. Corrosion-resistant, stainless steel captive screws speeds installation, minimize risk of lost parts, and withstand abuse. Adjustable mounting feet can be moved to center of unit for instant strut- or pole-mounting with



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007150131
Manufacturers Part Number	PS60SSAX
UPC	785007150131

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Non-Fusible Safety Switch with Auxiliary Contact

Packaging

Carton	1
Weight Per each	4.35

Uses, Certifications, and Standards

Application	Industrial
Enclosure	IP67 Suitability;NEMA Type 4X (watertight, hosedown), Type 12K (dusttight, falling dirt)
environmental conditions	Flammability: UL94 5VA and VO Classification;Moisture Resistance: Per UL50, Section 35, NEMA Enclosure Type 4X (watertight, hosedown), Type 12K (dusttight, falling dirt), and IP67 suitability;UV Resistance: All enclosure materials are UV stable
Mounting	External adjustable feet with five (5) positions. Can be mounted directly to channel or strut (no washers required).
standard	UL, CSA