



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PVC1 SCH 40 1" 10' PVC Conduit

Heritage Plastics

Catalog Number	PVC1
Manufacturer	Heritage Plastics
Description	PVC Conduit, Underground or Aboveground Application, Gray Color, 1.004 In Conduit Inner Diameter, 1.315 In Conduit Outer Diameter, 10 FT Length, Made In Usa, +90 °C Maximum Operating Temperature, 3600 FT/PK Package Quantity, Belled End;Corrosion Resistant:Rust Resistant:Sunlight Resistant;Rated For 90° Cable;Rigid Nonmetallic PVC Schedule 40 Special Features, Intertex Etl Listed Us;UI 651 and Nema TC2 Standards Met, 1 In Trade Size, 0.133 In Wall Thickness, 0.32 LB Weight
Weight per unit	0.3200 (lbs/each)
Product Category	PVC Conduit, Fittings, & Boxes

Features

Material	PVC
outside diameter	1.315

Dimensions and Weight

Diameter	1"
Height	1.315
Width	1.315

Descriptions

Description	SCH 40 1" 10' PVC CONDUIT
extra long description	AL-TUBE 8104 PVC SCH40 1 x 10 UL BE

Manufacturer Information

GTIN	00091111081040
Manufacturers Part Number	A52BA12
UPC	091111081040

Taxonomies, Classifications, and Categories

Category Description	Conduit & Raceways - Pvc Conduit, Fittings, & Boxes
	PVC Schedule 40 Conduit
Type	PVC - Sch 40/80

Availability

minimum qty	10
-------------	----

Packaging

Carton	100
Package	3600
Weight Per foot	0.32



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

UL651
