



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PVC12 SCH 40 1/2" 10' PVC Conduit

Heritage Plastics

Catalog Number	PVC12
Manufacturer	Heritage Plastics
Description	PVC Conduit, Underground or Aboveground Application, Gray Color, 0.578 In Conduit Inner Diameter, 0.840 In Conduit Outer Diameter, 10 FT Length, Made In Usa, +90 °C Maximum Operating Temperature, 6000 FT/PK Package Quantity, Belled End;Corrosion Resistant:Rust Resistant:Sunlight Resistant;Rated For 90° Cable;Rigid Nonmetallic PVC Schedule 40 Special Features, Intertex Etl Listed Us;UI 651 and Nema TC2 Standards Met, 1/2 In Trade Size, 0.109 In Wall Thickness, 0.162 LB Weight
Weight per unit	0.1620 (lbs/each)
Product Category	PVC Conduit, Fittings, & Boxes

Features

Material	PVC
outside diameter	0.84

Dimensions and Weight

Diameter	1/2"
Height	0.84
Size	1/2
Width	0.84

Descriptions

Description	SCH 40 1/2" 10' PVC CONDUIT
extra long description	AL-TUBE 8102 PVC SCH40 1/2 x 10 UL

Manufacturer Information

GTIN	00091111081026
Manufacturers Part Number	A52AE12
UPC	091111081026

Taxonomies, Classifications, and Categories

Category Description	PVC Schedule 40 Conduit
	Conduit & Raceways - Pvc Conduit, Fittings, & Boxes
Type	PVC - Sch 40/80

Availability

minimum qty	10
-------------	----

Packaging

Carton	100
Package	6000
Weight Per foot	0.162



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

UL651
