



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PVC4 SCH 40 4" 10' PVC Conduit

Heritage Plastics

Catalog Number	PVC4
Manufacturer	Heritage Plastics
Description	PVC Conduit, Underground or Aboveground Application, Gray Color, 3.961 In Conduit Inner Diameter, 4.500 In Conduit Outer Diameter, 10 FT Length, Made In Usa, +90 °C Maximum Operating Temperature, 570 FT/PK Package Quantity, Belled End;Corrosion Resistant;Rust Resistant;Sunlight Resistant;Rated For 90° Cable;Rigid Nonmetallic PVC Schedule 40 Special Features, Intertex Etl Listed Us;UI 651 and Nema TC2 Standards Met, 4 In Trade Size, 0.237 In Wall Thickness, 2.0669 LB Weight
Weight per unit	2.3 (lbs/each)
Product Category	PVC SCH 40 Conduit

Features

Material	PVC
outside diameter	4.5

Dimensions and Weight

Diameter	4"
Height	4.5
Width	4.5

Descriptions

Description	SCH 40 4" 10' PVC CONDUIT
extra long description	AL-TUBE 8116 PVC SCH40 4 x 10 UL BE

Manufacturer Information

GTIN	00091111081163
Manufacturers Part Number	A52EA12
UPC	091111081163

Taxonomies, Classifications, and Categories

Category Description	Conduit & Raceways - Pvc Conduit, Fittings, & Boxes
	PVC Schedule 40 Conduit
Type	PVC - Sch 40/80

Availability

minimum qty	10
-------------	----

Packaging

Carton	10
Package	570
Weight Per foot	2.292



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

UL651
