



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QHE4X32T8UNVISN *Delisted* (4)32W T8 Electronic Is Ballast *Sylvania-Ledvance*

Catalog Number	QHE4X32T8UNVISN
Manufacturer	Sylvania-Ledvance
Description	OBS49971 4 Lamp 32WT8 High Efficiency Instant Start Electronic Ballast, Universal Voltage, Normal Ballast Factor, Banded 10 PK.
Weight per unit	0.9590 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

amperage rating	120
Ballast Factor	0.88
Minimum Starting Temperature	-20.000000000000000
Number of Lamps	4
Power Factor	>0.97
start type	Instant Start
total harmonic distortion	<10

Dimensions and Weight

Height	1.1810000000000000
Length	9.4690000000000000
Width	1.6810000000000000

Descriptions

Description	*DELISTED* (4)32W T8 ELECTRONIC IS BALLAST
extra long description	SYL QHE-4X32T8/UNV-ISN-SC-B/49971 Q
Long Description	OBS49971 4 lamp 32wT8 High Efficiency Instant Start electronic ballast, universal voltage, normal ballast factor, banded 10 pk.
Product Type	QHE4X32T8UNVISNSCB 10/CS 1/Sku
Special Features	NO

Manufacturer Information

Brand	Ledvance LLC
GTIN	00046135499715
Manufacturers Part Number	QHE-4X32T8/UNV-ISN-SC-B/49971
UPC	046135499715

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Ballasts And Lighting Controls

Packaging

Carton	1
Package	10
Weight Per each	0.959