

# Eaton TR5362CDW

Catalog Number: TR5362CDW

Eaton Arrow Hart heavy duty industrial specification grade duplex receptacle, Tamper resistant, auto-grounding, Dual control, #14-10 AWG, 20A, Flush, 125V, White, Brass, Impact-resistant thermoplastic face, PVC body, 5-20R, 2-pole, 3-wire, ,



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle	TR5362CDW
	<b>UPC</b>
	032664744662
<b>Product Length/Depth</b>	<b>Product Height</b>
1.3 in	4.19 in
<b>Product Width</b>	<b>Product Weight</b>
0.84 in	0.22 lb
<b>Certifications</b>	
cULus Listed	

## Product specifications

### Device type

Receptacle

### Color

White

### Face/body material

PVC Body

Impact-resistant thermoplastic face

### Wiring method

Back and side

### Features

Tamper resistant

Auto-grounding

Dual-controlled

### Mounting method

Flush

### Allowable wire size

#14-10 AWG

### Amperage Rating

20A

### Number Of Poles

Two-pole

### Contact material

Brass

### Type

Dual control

### Device grade

Construction

### NEMA configuration

5-20R

### Style type

Standard

### Design type

Straight blade

### Connection type

Screw

## Resources

### Brochures

[Spec grade receptacles brochure](#)

[Controlled receptacles sell sheet](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - TR5362CDW](#)

Number of wires

Three-wire

Receptacle type

Duplex

Voltage rating

125V

Application

Industrial

Torque rating

14 lbf-inch



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)