



Product Quick Search

[HOME](#) | [WHERE TO BUY](#) | [CONTACT US](#) | [SITE MAP](#)

- [PRODUCTS](#)
- [SUPPORT](#)
- [NEWS/EVENTS](#)
- [ABOUT BALDOR](#)
- [INVESTOR RELATIONS](#)

General Information

- [Overview](#)
- [Specifications](#)
- [Performance Data](#)
- [Parts List](#)
- [Dimensional Dwg](#)
- [Connection Diag](#)
- [Product Literature](#)
- [More Information](#)
- [Locate Distributor](#)
- [Baldor Sales Offices](#)

[Return to List](#)

[AC Motors](#) | [Explosion Proof](#) |

Specifications: M7070T

Catalog Number:	M7070T
Specification Number:	37H239T977H1
Horsepower:	10
Voltage:	230/460
Hertz:	60
Phase:	3
Full Load Amps:	25.6/12.8
Usable at 208 Volts:	N/A
RPM:	1760
Frame Size:	215T
Service Factor:	1.00
Rating:	40C AMB-CONT
Locked Rotor Code:	J
NEMA Design Code:	B
Insulation Class:	B
Full Load Efficiency:	89.5
Power Factor:	81
Enclosure:	N/A
Baldor Type:	3738M
DE Bearing:	N/A
ODE Bearing:	N/A
Electrical Specification Number:	37WGT977
Mechanical Specification Number:	37H239
Base:	RG
Mounting:	F1

* For certified information, contact your local [Baldor office](#).