



Product Quick Search



[HOME](#) | [WHERE TO BUY](#) | [CONTACT US](#) | [SITE MAP](#)

- [PRODUCTS](#)
- [SUPPORT](#)
- [NEWS/EVENTS](#)
- [ABOUT BALDOR](#)
- [INVESTOR RELATIONS](#)

General Information

- [Overview](#)
- [Specifications](#)
- [Performance Data](#)
- [Parts List](#)
- [Dimensional Dwg](#)
- [Connection Diag](#)
- [Product Literature](#)
- [More Information](#)
- [Locate Distributor](#)
- [Baldor Sales Offices](#)

◀ [Return to List](#)

[AC Motors](#) | [General Purpose](#) |

Specifications: VM3538

Catalog Number:	VM3538
Specification Number:	34A63-872
Horsepower:	1/2
Voltage:	230/460
Hertz:	60
Phase:	3
Full Load Amps:	2/1
Usable at 208 Volts:	2.5
RPM:	1725
Frame Size:	56C
Service Factor:	1.25
Rating:	40C AMB-CONT
Locked Rotor Code:	L
NEMA Design Code:	B
Insulation Class:	B
Full Load Efficiency:	74
Power Factor:	63
Enclosure:	TEFC
Baldor Type:	3416M
DE Bearing:	6203
ODE Bearing:	6203
Electrical Specification Number:	34WG0872
Mechanical Specification Number:	34A063
Base:	N
Mounting:	F1

* For certified information, contact your local [Baldor office](#).