



[Home](#)
[Applications](#)
[Products](#)
[Where To Buy](#)
[What's New](#)
[Support](#)
[About Us](#)

Product Search

Product Home

Features

Specifications

Models, Pricing, Options,  
Accessories

Manuals

Product Registration

Digital Multimeters >

## Fluke 12 Digital Multimeter

Specifications	
<b>Voltage DC</b>	<b>Range and Resolution:</b> 4000 mV*, 4.000V, 40.00V, 400V, 600V <b>Best Accuracy:</b> Model 10 $\pm(1.5\%+1)$ Model 11 $\pm(0.9\%+1)$ Model 12 $\pm(0.9\%+1)$
<b>Voltage AC</b>	<b>Range and Resolution:</b> 4000 mV, 4.000V, 40.00V, 400V, 600V Model 10 $\pm(2.9\%+3)$ <b>Best Accuracy:</b> Model 11 $\pm(1.9\%+3)$ Model 12 $\pm(1.9\%+3)$
<b>Resistance</b>	<b>Range and Resolution:</b> 400.0 $\Omega$ , 4.000 k $\Omega$ , 40.00 k $\Omega$ , 400.0 k $\Omega$ , 4.000 M $\Omega$ , 40.00 M $\Omega$ <b>Best Accuracy:</b> Model 10 $\pm(1.5\%+1)$ Model 11 $\pm(0.9\%+1)$ Model 12 $\pm(0.9\%+1)$
<b>Capacitance</b>	<b>Range and Resolution:</b> 1.000 $\mu$ F, 10.00 $\mu$ F, 100.0 $\mu$ F, 1000 $\mu$ F, 10,000 $\mu$ F <b>Best Accuracy:</b> Model 10 N/A Model 11 $\pm(1.9\%+2)$ Model 12 $\pm(1.9\%+2)$
<b>Note</b>	*Available in manual mode. Use this range with accessories.

Mechanical & General Specifications	
<b>Size</b>	142.3 mm L x 70.5 mm W x 34.6 mm
<b>Weight</b>	286g
<b>Warranty</b>	Three years, one year guaranteed calibration
<b>Battery Life</b>	<b>Alkaline:</b> 650 hours continuous <b>Carbon-zinc:</b> 450 hours continuous

© 1995 - 2007 Fluke Corporation

[Privacy Statement](#)

[Disclaimer](#)