



## SNA Terminal Blocks T&B Catalog Number:

010500127

**UPC Number:**

66201995344

**Status:**

Active

**Description:**

Green, feed through terminal block with 6 mm spacing, 30 Amp rated UL current with screw clamp connection that accepts 22-10 AWG UL wire range

### Features

Self-locking clamp design prevents screw loosening

Funneled side entry for up to two ferruled or non-ferruled solid or stranded wires

Touch-safe IP20 protection

High quality steel offers a very high over-torque resistance

Compensates for the flattening of copper under contact pressure

Clamp is protected from harsh environments by a zinc bichromate surface treatment

### Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

### General

Style	Feed Through
Color	Green
Mounting	DIN 1-3
Series	M 4/6
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-10
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	4
Rated CSA Wire Size (AWG)	10

### Dimension Information

L x W x H (mm)	44.5 x 6 x 53
Spacing (mm)	6
L x W x H (in)	1.75 x 0.238 x 2.18
Spacing (inches)	0.236

### Specifications

UL Current (Amps)	30
UL Voltage (VAC)	600
Rated UL Wire Size (AWG)	10
IEC Voltage (VAC)	800
IEC Current (Amps)	32
CSA Voltage (VAC)	600
CSA Current (Amps)	25

### Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	2000

T&B Sold in UOM	Each
T&B Weight Per UOM	0.01 lbs. Each

## Certifications

Approvals	UL, IEC, CSA
-----------	--------------

## Certifications



### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)



**SNA Terminal Blocks**  
**T&B Catalog Number:**

010500127

**UPC Number:**

66201995344

**Status:**

Active

**Description:**

Green, feed through terminal block with 6 mm spacing, 30 Amp rated UL current with screw clamp connection that accepts 22-10 AWG UL wire range

**Features**

- Self-locking clamp design prevents screw loosening
- Funneled side entry for up to two ferruled or non-ferruled solid or stranded wires
- Touch-safe IP20 protection
- High quality steel offers a very high over-torque resistance
- Compensates for the flattening of copper under contact pressure
- Clamp is protected from harsh environments by a zinc bichromate surface treatment

**Application**

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

**General**

Style	Feed Through
Color	Green
Mounting	DIN 1-3
Series	M 4/6
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-10
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	4
Rated CSA Wire Size (AWG)	10

**Dimension Information**

L x W x H (mm)	44.5 x 6 x 53
Spacing (mm)	6
L x W x H (in)	1.75 x 0.238 x 2.18
Spacing (inches)	0.236

**Specifications**

UL Current (Amps)	30
UL Voltage (VAC)	600
Rated UL Wire Size (AWG)	10
IEC Voltage (VAC)	800
IEC Current (Amps)	32
CSA Voltage (VAC)	600
CSA Current (Amps)	25

**Packaging**

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	2000

T&B Sold in UOM	Each
T&B Weight Per UOM	0.01 lbs. Each

## Certifications

Approvals	UL, IEC, CSA
-----------	--------------

## Certifications



### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)