



**SNA Terminal Blocks**  
**T&B Catalog Number:**

012512603

**UPC Number:**

66201995895

**Status:**

Active

**Description:**

Blue double-deck terminal blocks with 6 mm spacing, 20 Amp rated UL current that accepts 12 AWG UL wire

**Features**

Includes IP20 protection

**Application**

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

**General**

Style	Double Deck Feed Through
Color	Blue
Mounting	DIN 1-3
Series	M4/6.D2.1.N
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-12
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	4
Rated CSA Wire Size (AWG)	12

**Dimension Information**

L x W x H (mm)	65.5 x 64.5
Spacing (mm)	6
L x W x H (in)	2.57 x 2.54
Spacing (inches)	0.238

**Specifications**

UL Current (Amps)	20
UL Voltage (VAC)	300
Rated UL Wire Size (AWG)	12
IEC Voltage (VAC)	800
IEC Current (Amps)	32

**Packaging**

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	1000
T&B Sold in UOM	Each
T&B Weight Per UOM	3.5 lbs. per 100

**Certifications**

Approvals	IEC, UL, CSA
-----------	--------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com