



SNA Terminal Blocks
T&B Catalog Number:

016511417
 66201996021
 Active

UPC Number:
Status:
Description:

Green and yellow ground block with screw clamp connection, 8 mm spacing on a DIN 3 rail, screws onto rail

Features

- Top entry wire connection
- Touch-safe IP20 protection

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style	Ground Block
Color	Green and Yellow
Mounting	DIN 3
Series	M 6/8.P
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-8
Rated IEC Wire Range (Solid) (mm ²)	0.5 - 10
Rated IEC Wire Range (Stranded) (mm ²)	0.5 - 6

Dimension Information

L x W x H (mm)	43.5 x 8 x 48
Spacing (mm)	8
L x W x H (in)	1.72 x .315 x 1.89
Spacing (inches)	.315

Specifications

Rated UL Wire Size (AWG)	8
--------------------------	---

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	750
T&B Sold in UOM	Each
T&B Weight Per UOM	0.06 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com



SNA Terminal Blocks
T&B Catalog Number:

016511417

UPC Number:

66201996021

Status:

Active

Description:

Green and yellow ground block with screw clamp connection, 8 mm spacing on a DIN 3 rail, screws onto rail

Features

Top entry wire connection

Touch-safe IP20 protection

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style	Ground Block
Color	Green and Yellow
Mounting	DIN 3
Series	M 6/8.P
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-8
Rated IEC Wire Range (Solid) (mm ²)	0.5 - 10
Rated IEC Wire Range (Stranded) (mm ²)	0.5 - 6

Dimension Information

L x W x H (mm)	43.5 x 8 x 48
Spacing (mm)	8
L x W x H (in)	1.72 x .315 x 1.89
Spacing (inches)	.315

Specifications

Rated UL Wire Size (AWG)	8
--------------------------	---

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	750
T&B Sold in UOM	Each
T&B Weight Per UOM	0.06 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com