



**SNA Terminal Blocks**  
**T&B Catalog Number:**

019909513

**UPC Number:**

66201996499

**Status:**

Active

**Description:**

Black, fuse holder block with 13 mm spacing, 25 Amp rated UL current with screw clamp connection that accepts 22 - 10 AWG UL wire range

**Features**

- Self-locking clamp design prevents screw loosening
- Quick fuse installation and replacement
- Touch-safe IP20 protection
- High quality steel offers a very high over-torque resistance
- Compensates for the flattening of copper under contact pressure
- Clamp is protected from harsh environments by a zinc bichromate surface treatment

**Application**

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

**General**

Style	Fuse Holder
Color	Black
Mounting	DIN 1-3
Series	ML 10/13.SF
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-10
Rated IEC Wire Range (Solid) (mm <sup>2</sup> )	10
Rated CSA Wire Size (AWG)	8

**Dimension Information**

L x W x H (mm)	85 x 32 x 70.5
Spacing (mm)	13
L x W x H (in)	3.35 x 1.25 x 2.77
Spacing (inches)	0.512

**Specifications**

UL Current (Amps)	25
UL Voltage (VAC)	600
Rated UL Wire Size (AWG)	10
IEC Voltage (VAC)	800
IEC Current (Amps)	16
CSA Voltage (VAC)	600
CSA Current (Amps)	25

**Packaging**

T&B Order Multiple	20
T&B Inner Pack	20
Package in Units	200
T&B Sold in UOM	Each
T&B Weight Per UOM	0.12 lbs. Each

## Certifications

Approvals

UL, IEC, CSA

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)