



Product Description

Effectively removes grease, oil, tar, etc. to increase operating efficiency of equipment. It evaporates quickly, leaves no residue and has no flash or fire point, making it an excellent alternative to 1,1,1-based cleaners. Use caution on some plastics.

Product Specifications

Applications	Air tools, mechanical brakes, clutches, chains, wire ropes, motors, dies, molds, parts, bearings, generators & compressors.
Unit Package Description	5 Gallon Pail
Generic Description 1	Heavy Duty Degreaser
Brand	CRC
Net Fill	5 Gal
UPC Code	0 78254 02021 1
Unit Dimensions-Inches	13.75H x 11.25W x 11.25D
Units Per Case	1
Case Dimensions-Inches	11.1H x 10.6W x 13.1D
Cases Per Pallet	24
Lbs. Per Case	62.5
Appearance	Colorless Liquid
Odor	Chlorinated Solvent
Base Type	Chlorinated
Flashpoint - TCC Method	None
Specific Gravity	1.544
KB Value	117
Flammability	Non-flammable
Plastic Safe	No
Evaporation Rate	>1 (butyl acetate=1)
Dielectric Strength	36,800 Volts
Propellant	None
NSF Category Code	K1
NSF Registered	Yes
NSF Number	017217
DOT Proper Shipping Name	Tetrachloroethylene
VOC % (Federal)	45
VOC g/L (Federal)	694.8
VOC Lbs./Gal. (Federal)	5.8
Compliant For CA	Yes
VOC Category	Energized Electrical Cleaner
CA VOC Limit	None
OTC VOC Limit	None



Product Description

Effectively removes grease, oil, tar, etc. to increase operating efficiency of equipment. It evaporates quickly, leaves no residue and has no flash or fire point, making it an excellent alternative to 1,1,1-based cleaners. Use caution on some plastics.

Product Specifications

Applications	Air tools, mechanical brakes, clutches, chains, wire ropes, motors, dies, molds, parts, bearings, generators & compressors.
Unit Package Description	5 Gallon Pail
Generic Description 1	Heavy Duty Degreaser
Brand	CRC
Net Fill	5 Gal
UPC Code	0 78254 02021 1
Unit Dimensions-Inches	13.75H x 11.25W x 11.25D
Units Per Case	1
Case Dimensions-Inches	11.1H x 10.6W x 13.1D
Cases Per Pallet	24
Lbs. Per Case	62.5
Appearance	Colorless Liquid
Odor	Chlorinated Solvent
Base Type	Chlorinated
Flashpoint - TCC Method	None
Specific Gravity	1.544
KB Value	117
Flammability	Non-flammable
Plastic Safe	No
Evaporation Rate	>1 (butyl acetate=1)
Dielectric Strength	36,800 Volts
Propellant	None
NSF Category Code	K1
NSF Registered	Yes
NSF Number	017217
DOT Proper Shipping Name	Tetrachloroethylene
VOC % (Federal)	45
VOC g/L (Federal)	694.8
VOC Lbs./Gal. (Federal)	5.8
Compliant For CA	Yes
VOC Category	Energized Electrical Cleaner
CA VOC Limit	None
OTC VOC Limit	None