



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



07401027 STR Male, DCG, 1.0-1.1", 1.25" W/Mesh *Hubbell Wiring Devices*

Catalog Number	07401027
Manufacturer	Hubbell Wiring Devices
Description	Kellems Wire Management, Deluxe Cord Grips, Straight Male, 1.000-1.125", 1 1/4" With Mesh
Weight per unit	0.4000 (lbs/each)
Product Category	Cable & Cord Grips

Features

Material	Aluminum Fittings, Stainless Steel Mesh
Number of Conductors	Single
pallet quantity	600

Material, Color, and Finish

Color	Metallic
-------	----------

Dimensions and Weight

Size	1 1/4" NPT
------	------------

Descriptions

Description	STR MALE, DCG, 1.0-1.1", 1.25" W/MESH
extra long description	HWDK 07401027 STR MALE, DCG, 1.0-1.
Features	Deluxe cord grips help to alleviate pull tension on terminals, control cable arc-of-bend, prevent cord pull-out and provide a Liquidtight seal. They are offered with either aluminum, stainless steel or nylon fittings in a variety of configurations and NPT thread sizes. Additionally, a completely non-metallic product is available. Specific uses are: wiring enclosures, pendant stations, hand tools, construction, processing and material handling equipment, pumps, motors and machine tools.
Long Description	Kellems Wire Management, Deluxe Cord Grips, Straight Male, 1.000-1.125", 1 1/4" with Mesh
Product Type	STR Male, DCG, 1.0-1.1", 1.25" W/Mesh
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585322087
Manufacturers Part Number	07401027
series	Deluxe Cord Grips
UPC	783585322087



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Straight Male Thread

Packaging

Carton	1
Package	5
Weight Per each	0.4

Uses, Certifications, and Standards

Application	Straight Male- Form 5
environmental conditions	Suitable For Use In Wet Locations When Used With A Listed Sealing Ring Between Box And Fitting.
Mounting	Locknut or Tapped Opening
standard	UL Listed
Temperature Rating	Minimum -30 Deg F to 240 Deg F (-34 Deg C to 115 Deg C)