



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



076058800 400W MH Temp Fixture

Southwire Company

Catalog Number	076058800
Manufacturer	Southwire Company
Description	400W Metal Halide Light Fixture Wire Guard W/Bottom Pulse Start Type O
Weight per unit	20.9 (lbs/ft)
Product Category	Lighting

Features

amperage rating	2.2
average life	10000
Ballast Type	ANSI M155
Base	Metal
Lamp Type	Pulse Start
Number of Lamps	1
Shape	Round
Voltage Rating	125
Wattage	400

Material, Color, and Finish

color temperature	4000K
-------------------	-------

Dimensions and Weight

Size	10" dia / 23" high
------	--------------------

Descriptions

Description	400W MH TEMP FIXTURE
extra long description	SWC 7605SW LIGHT, SECURITY 400W MET
Long Description	400W METAL HALIDE LIGHT FIXTURE WIRE GUARD W/BOTTOM PULSE START TYPE O
Product Type	Light, Security 400W Metal Halide

Manufacturer Information

Brand	Cables & Cords
GTIN	00029892509538
Manufacturers Part Number	7605SW
UPC	029892509538

Taxonomies, Classifications, and Categories

Category Description	Outdoor HID Lighting
Type	Portable Light

Packaging

Carton	1
Weight Per foot	20.85



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Type Portable O
standard	UL Listed