



## Open Switches T&B Catalog Number:

**UPC Number:**  
**Status:**  
**Description:**

OT40FT3  
80432541557  
Active

3 pole, 40 amps rated at 600 VAC, UL 508, door mounted open non-fusible disconnect switch

### Features

Quick make, quick brake mechanism  
Extremely compact size  
Finger-proof construction with no hazardous exposed parts

### Application

Industrial control panel disconnects  
For use in motor controller and motor overload protection applications  
Can be used as an OSHA lockout/tagout disconnect

### General

|                 |              |
|-----------------|--------------|
| Style           | Door Mounted |
| Number of Poles | 3            |
| Series          | Non-fusible  |

### Approvals

|          |        |
|----------|--------|
| UL Class | UL 508 |
|----------|--------|

### Dimension Information

|                    |                    |
|--------------------|--------------------|
| H x W x D (inches) | 2.13 x 1.69 x 2.64 |
|--------------------|--------------------|

### Specifications

|                      |     |
|----------------------|-----|
| Rated Current (Amps) | 40  |
| Rated Voltage AC     | 600 |

### Packaging

|                    |                |
|--------------------|----------------|
| T&B Inner Pack     | 1              |
| Package in Units   | 10             |
| T&B Sold in UOM    | Each           |
| T&B Weight Per UOM | 0.23 lbs. Each |

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com



## Open Switches T&B Catalog Number:

**UPC Number:** OT40FT3  
**Status:** 80432541557  
**Description:** Active

3 pole, 40 amps rated at 600 VAC, UL 508, door mounted open non-fusible disconnect switch

### Features

Quick make, quick brake mechanism  
 Extremely compact size  
 Finger-proof construction with no hazardous exposed parts

### Application

Industrial control panel disconnects  
 For use in motor controller and motor overload protection applications  
 Can be used as an OSHA lockout/tagout disconnect

### General

Style Door Mounted  
 Number of Poles 3  
 Series Non-fusible

### Approvals

UL Class UL 508

### Dimension Information

H x W x D (inches) 2.13 x 1.69 x 2.64

### Specifications

Rated Current (Amps) 40  
 Rated Voltage AC 600

### Packaging

T&B Inner Pack 1  
 Package in Units 10  
 T&B Sold in UOM Each  
 T&B Weight Per UOM 0.23 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com