



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## OTM10 250V 10A 1 1/2X13/32 Mid Fuse

*Mersen Fuses*

Catalog Number	OTM10
Manufacturer	Mersen Fuses
Description	Fuse Otm - Midget - Fast-Acting 250VAC 10A Ferrule Amp-Trap®
Weight per unit	0.0120 (lbs/each)
Product Category	Small Dimension Fuses

### Features

AC Voltage Rating	250
amperage rating	10
class	Midget
connection	Ferrule
interrupt rating	10
Voltage Rating	250

### Material, Color, and Finish

Body Material	Paper
---------------	-------

### Dimensions and Weight

Size	1.5 x 0.41
------	------------

### Descriptions

Description	250V 10A 1 1/2X13/32 MID FUSE
extra long description	Mersen OTM10 Fuse OTM - Midget - Fa
Features	One-Time OTM midget fuses provide low-cost protection for 250VAC general purpose lighting, heating, control circuits, etc. where time-delay is not required. (Not for Branch Circuit Protection).
Long Description	Fuse OTM - Midget - Fast-Acting 250VAC 10A Ferrule Amp-Trap®
Product Type	Fuse Otm - Midget - Fast-Acting 250VAC 10A Ferrule
Short Description	250V 10A 1 1/2x13/32 MID FUSE
Special Features	Low cost and fully rated for economy without compromise Can be used with UltraSafe™ fuse holders 1 1/2" x 13/32" (10 mm x 38 mm) dimensions

### Manufacturer Information

Brand	Mersen
GTIN	00782001705107
Manufacturers Part Number	OTM10
UPC	782001705107

### Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	Midget Fuses



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.012

## Uses, Certifications, and Standards

Application	Supplemental protection of circuits up to 250VAC and 10kA
Mounting	Clip
standard	UL Listed to standard 248-14, File E33925 CSA Certified to Standard C22.2 No. 248.14