



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1008694ACH 20A MTR SCKT Instrument Rated 13 Term

Eaton Corp

Catalog Number	1008694ACH
Manufacturer	Eaton Corp
Description	Eaton Meter Socket, Instrument Rated Socket, 20A, Over/Under, 1 In Bolt-On Hub, 13-Jaw, Factory Wired Test Switch, 600 Vac, 3-Phase, Four-Wire
Weight per unit	15.0 (lbs/each)
Product Category	Commercial Single Meter Socket

Features

amperage rating	20A
dimensions	4.3600 IN X 12.0000 IN X 20.0000 IN
Phase	Three-phase
Voltage Rating	600 V

Descriptions

Description	20A MTR SCKT INSTRUMENT RATED 13 TERM
extra long description	ETN 1008694ACH MtrSkt,20A,Ringless,
Features	Eaton is your one-stop shop for the widest range of residential and light commercial electric meter sockets in the industry. These single-socket surface- or flush-mount outdoor enclosures come in two styles, allowing for both easy, cost-saving installation, and for the use of BR- or CH-type branch breakers. The one-piece, die-run electric meter socket enclosures eliminate tampering and extend product life. These are utility approved and can be used for residential meter socket installations, rural service
Long Description	Eaton meter socket, Instrument rated socket, 20A, Over/under, 1 in bolt-on hub, 13-jaw, Factory wired test switch, 600 Vac, 3-phase, four-wire
Product Type	MTRSKT, 20A, Ringless, 13-Jaw, Oh/Ug

Manufacturer Information

Brand	Eaton
GTIN	00782116176045
Manufacturers Part Number	1008694ACH
UPC	782116176045

Taxonomies, Classifications, and Categories

Type	Meter socket
------	--------------

Packaging

Carton	1
Weight Per each	15



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Residential Bldgs & Facilities - Residential Bldgs & Facilities -

Other

standard

UL Listed