



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 30.5 mm, Heavy-Duty Selector Switch Operator

10250T15712

UPC:782113312613

### Dimensions:

- **Height:** 2.2 IN
- **Length:** 2 IN
- **Width:** 1.8 IN

**Weight:** .4 LB

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Key
- **Cam Code:** Cam 1
- **Illumination:** Non-illuminated
- **Key Removal Position:** Left only
- **Number Of Positions:** Two-position
- **Product Category:** Selector switch
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T
- **Throw Type:** 60°

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Cam selection for pushbutton selectors](#)

### Certifications:

- UL Listed
- CSA Certified

### Product compliance:

- CE Marked







Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 30.5 mm, Heavy-Duty Selector Switch Operator

10250T15712

UPC:782113312613

### Dimensions:

- **Height:** 2.2 IN
- **Length:** 2 IN
- **Width:** 1.8 IN

**Weight:** .4 LB

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Key
- **Cam Code:** Cam 1
- **Illumination:** Non-illuminated
- **Key Removal Position:** Left only
- **Number Of Positions:** Two-position
- **Product Category:** Selector switch
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T
- **Throw Type:** 60°

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Cam selection for pushbutton selectors](#)

### Certifications:

- UL Listed
- CSA Certified

### Product compliance:

- CE Marked



