



Powering Business Worldwide

pe.eaton.com

Eaton Heavy-duty assembled selector switch

10250T21KB-POP

UPC:786685393902

Dimensions:

- **Height:** 3 IN
- **Length:** 7 IN
- **Width:** 5 IN

Weight:.1 LB

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Knob
- **Actuator Color:** Black
- **Contact Configuration:** 2NO
- **Illumination:** Non-illuminated
- **Number Of Positions:** Three-position
- **Operating Mode:** Maintained
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T
- **Throw Type:** 60°

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Quick Selector - 10250T Pilot Devices](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:

- CE Marked





Powering Business Worldwide

pe.eaton.com

Eaton Heavy-duty assembled selector switch

10250T21KB-POP

UPC:786685393902

Dimensions:

- **Height:** 3 IN
- **Length:** 7 IN
- **Width:** 5 IN

Weight:.1 LB

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Knob
- **Actuator Color:** Black
- **Contact Configuration:** 2NO
- **Illumination:** Non-illuminated
- **Number Of Positions:** Three-position
- **Operating Mode:** Maintained
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T
- **Throw Type:** 60°

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Quick Selector - 10250T Pilot Devices](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:

- CE Marked



