



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 30.5 mm, Heavy-Duty Selector Switch Operator

10250T3043

UPC:782113226965

### Dimensions:

- **Height:** 2.3 IN
- **Length:** 2 IN
- **Width:** 1.9 IN

**Weight:** .25 LB

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Lever
- **Actuator Color:** Black
- **Cam Code:** Cam 3
- **Illumination:** Non-illuminated
- **Number Of Positions:** Three-position
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T
- **Throw Type:** 60°

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T3043](#)

### Certifications:

- UL Listed
- CSA Certified

### Product compliance:

- CE Marked





Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 30.5 mm, Heavy-Duty Selector Switch Operator

10250T3043

UPC:782113226965

### Dimensions:

- **Height:** 2.3 IN
- **Length:** 2 IN
- **Width:** 1.9 IN

**Weight:** .25 LB

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator:** Lever
- **Actuator Color:** Black
- **Cam Code:** Cam 3
- **Illumination:** Non-illuminated
- **Number Of Positions:** Three-position
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T
- **Throw Type:** 60°

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T3043](#)

### Certifications:

- UL Listed
- CSA Certified

### Product compliance:

- CE Marked

