



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Assembled, 30.5 mm Pushbutton

10250T30B

UPC:782113357829

### Dimensions:

- **Height:** 3.2 IN
- **Length:** 2.4 IN
- **Width:** 2.1 IN

**Weight:** .3 LB

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator Color:** Black
- **Actuator Material:** Plastic
- **Bezel:** Chrome
- **Contact Configuration:** 1NO-1NC
- **Illumination:** Non-illuminated
- **Mounting:** Flush
- **Operating Mode:** Momentary
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T30B](#)

### Certifications:

- CSA Certified
- UL Listed

### Product compliance:

- CE Marked







Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Assembled, 30.5 mm Pushbutton

10250T30B

UPC:782113357829

### Dimensions:

- **Height:** 3.2 IN
- **Length:** 2.4 IN
- **Width:** 2.1 IN

**Weight:** .3 LB

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator Color:** Black
- **Actuator Material:** Plastic
- **Bezel:** Chrome
- **Contact Configuration:** 1NO-1NC
- **Illumination:** Non-illuminated
- **Mounting:** Flush
- **Operating Mode:** Momentary
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T

### Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T30B](#)

### Certifications:

- CSA Certified
- UL Listed

### Product compliance:

- CE Marked



