



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1046850 120V Ac/DC Smoke 10 Yr Life - UI 217 8TH

BRK Brands/Ademco/First Alert

| | |
|------------------|---|
| Catalog Number | 1046850 |
| Manufacturer | BRK Brands/Ademco/First Alert |
| Description | Hardwired Smoke Alarm With 10-Year Locked 9V Lithium Battery Backup. Ac 120V Interconnectable With Silence and Latching Features. Includes Ionization Smoke Sensing Technology. |
| Weight per unit | 0.6000 (lbs/each) |
| Product Category | Builders Products |

Features

| | |
|------------|-------------------------|
| dimensions | 2.25 in 5.69 in 5.69 in |
|------------|-------------------------|

Material, Color, and Finish

| | |
|-------|-------|
| Color | White |
|-------|-------|

Descriptions

| | |
|------------------------|---|
| extra long description | BRK 1046850 |
| Features | Hardwired smoke alarm with 10-Year locked 9V lithium battery backup |
| Long Description | Hardwired smoke alarm with 10-Year locked 9V lithium battery backup. AC 120V Interconnectable with Silence and Latching features. Includes Ionization smoke sensing technology. |
| Product Type | Alarm Smoke Ac/DC10 SMI105-Ac Box |
| Special Features | Battery Backup,End-of-Life Warning,Hardwire Interconnectivity,Hardwire Quick Connect Plug Included,Precision Detection |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | BRK |
| GTIN | 00029054022516 |
| Manufacturers Part Number | 1046850 |
| UPC | 029054022516 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------|
| Category Description | SMOKE DETECTORS |
| Type | SMOKE ALARM |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.6 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Precision Detection |
| standard | Conforms to UL 217 8th Edition Standard |