




PushGard™ Connectors

Simple, Secure, and Easy to Use alternative to traditional twist-on connectors.

Great for:

- Remodel Projects
- DIY Projects
- Light Fixtures
- Ceiling Fans
- Outlets
- Switches & Dimmer Controls

- Easy to Understand—2 ports connect 2 wires, 3 ports connect 3 wires etc.
- Fast Installation—Strip wire and insert into connector—No twisting or taping required
- Secure connections—Stainless steel springs firmly grip wires and restrict pull out
- Confident Connections—Continuity test point for easy voltage checks (3, 4, & 8 port connectors only)
- Simple Corrections—Remove wire from the connector with a left to right twist and pull and rewire
- Quick Identification—Clear polycarbonate shells with color coded side panels provide connection verification and identification
- Rated for 600V max in building wire or 1000V max in lighting fixtures & luminaires
- Use with Solid Copper Wire from #22–#12 AWG
- UL Listed



Ports	Part #	Pkg Qty	Wire Range
2	10-PC2	100/box	#22–#12 AWG Solid (connections rated at 600V Max.)
	19-PC2	10/clam	
3	10-PC3	100/box	
	19-PC2	10/clam	
4	10-PC4	100/box	
	19-PC2	10/clam	
8	10-PC8	50/box	
	19-PC8	10/clam	

