



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1101 40A 120V SPST Metal Indoor Time Clock

Nsi Industries

Catalog Number	1101
Manufacturer	Nsi Industries
Description	24 Hour Time Switch 40A 120V SPST Indoor Metal Enclosur
Weight per unit	2.4 (lbs/each)
Product Category	Electromechanical Time Switches

Features

action	MAGNETIC
Base	Screw
Contact Rating	120 VAC
Number of Pins	12 Pair
Phase	1 in
Poles	1 IN
Timing Range	TFKUVA10

Dimensions and Weight

Size	L=4.687 - H=7.937 - W=2.937 IN
------	--------------------------------

Descriptions

Description	40A 120V SPST METAL INDOOR TIME CLOCK
extra long description	NSI 1101 24 Hour Time Switch 40A 12
Long Description	24 Hour Time Switch 40A 120V SPST Indoor Metal Enclosur
Product Type	24 Hour Time Switch 40A 120V SPST Ind
Special Features	SPST 24 Hour Time Switch - Same Day On-Off Times Each Day

Manufacturer Information

Brand	98010027731
GTIN	00786261100115
Manufacturers Part Number	1101
sub brand	TORK Mechanical Time Controls
UPC	786261100115

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	24 Hour Time Switch

Packaging

Carton	1
Package	12
Weight Per each	2.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Lighting-Pumps-Signs-Air Conditioning-Watr Heaters-Fan Control
Enclosure	NEMA 1 Metal Indoor
environmental conditions	-40 to 165 F
Frequency Rating	60 Hz
Mounting	Screw Mount
Operating Temperature	-40 to 165 F
standard	UL-CSA