



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1104B DPST 40A Time Switch

Nsi Industries

| | |
|------------------|--|
| Catalog Number | 1104B |
| Manufacturer | Nsi Industries |
| Description | Time Switch, Metal Enclosure Material, 24 H Time Setting Mode, 75 (Min) Off;20 (Min) On Time Setting, 24 H Time Setting, DPST Contact Configuration, 208 to 277 V Ac @ 60 HZ, 40 A, Screw Connection, Metal Material, -40 °F Operating Temperature, +165 °F Operating Temperature, 4-11/16 X 2-15/16 X 7-15/16 In Size, 2.4 LB |
| Weight per unit | 2.4 (lbs/each) |
| Product Category | Mechanical Time Switches |

Features

| | |
|----------------|--------------|
| action | DPST |
| Base | Screw |
| Contact Rating | 208-277 VAC |
| Number of Pins | 12 Pair |
| Phase | Single Phase |
| Poles | 1 |
| Timing Range | 24 Hour |

Descriptions

| | |
|------------------------|--|
| Description | DPST 40A TIME SWITCH |
| extra long description | TORK 1104B 24 Hour Time Switch 40A |
| Features | 24 Hour Time Switch 40A 208-277V DPST Indoor Metal Enclosure |
| Special Features | DPST 24 Hour Time Switch - Same Day On-Off Times Each Day |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00786261100672 |
| UPC | 786261100672 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | TIME CLOCKS |
| Type | 24 Hour Time Switch |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 2.4 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---------------------|
| Enclosure | NEMA 1 Metal Indoor |
| environmental conditions | -40 to 165 F |
| Frequency Rating | 60 Hz |
| Mounting | Screw Mount |
| Operating Temperature | -40 to 165 F |
| standard | UL-CSA |