



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1104BPC DPST 208-277V 40a

Nsi Industries

Catalog Number	1104BPC
Manufacturer	Nsi Industries
Description	Time Switch, Plastic Enclosure Material, 24 H Time Setting Mode, 24 H Time Setting, DPST Contact Configuration, 277 V, 40 A, 1 Pole, Plastic, -40 °F Operating Temperature, +165 °F Operating Temperature, 5-1/16 X 3-1/16 X 8-5/16 In Size, 3.4 LB
Weight per unit	3.4 (lbs/each)
Product Category	Mechanical Time Switches

Features

action	DPST
Base	Screw
Contact Rating	208-277 VAC
Number of Pins	12 Pair
Phase	Single Phase
Poles	1
Timing Range	24 Hour

Descriptions

Description	DPST 208-277V 40A
extra long description	TORK 1104B-PC 24 Hr Time Switch 40A

Manufacturer Information

GTIN	00786261100979
UPC	786261100979

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	24 Hour Time Switch

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	3.4

Uses, Certifications, and Standards

Enclosure	NEMA 3R Polycarbonate Outdoor with Clear Cover
environmental conditions	-40 to 165 F
Frequency Rating	60 Hz
Mounting	Screw Mount
Operating Temperature	-40 to 165 F
standard	UL-CSA