



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1106DC 1-1/2" Diecast Chased Nipple

*Bridgeport Fittings*

|                  |   |
|------------------|---|
| Catalog Number   | 1106DC  |
| Manufacturer     | Bridgeport Fittings   |
| Description      | Conduit Chased Nipple, 1-1/2 In Trade Size, Hex Shape, Threaded Connection, 11/16 In Thread Length, 2-3/8 In Width, 0.2000 LB |
| Weight per unit  | 0.2000 (lbs/each)   |
| Product Category | Rigid Conduit Fittings - Steel  |

### Features

|          |               |
|----------|---------------|
| Material | Zinc Die Cast |
| media    | Yes           |

### Material, Color, and Finish

|        |              |
|--------|--------------|
| Finish | Ball burnish |
|--------|--------------|

### Dimensions and Weight

|        |       |
|--------|-------|
| Length | 1.375 |
| Size   | 1 1/2 |

### Descriptions

|                        |                                    |
|------------------------|------------------------------------|
| Description            | 1-1/2" DIECAST CHASED NIPPLE       |
| extra long description | BPT 1106-DC 1 1/2" CONDUIT NIPPLE, |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Bridgeport     |
| GTIN  | 00781747911063 |
| UPC   | 781747911063   |

### Taxonomies, Classifications, and Categories

|                      |                                |
|----------------------|--------------------------------|
| Category Description | DIECAST OFFSET & CHASE NIPPLES |
| Type                 | Conduit Nipple                 |

### Trade Size

|            |     |
|------------|-----|
| Trade Size | 1.5 |
|------------|-----|

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 10  |
| Package         | 100 |
| Weight Per each | 0.2 |

### Uses, Certifications, and Standards

|          |       |
|----------|-------|
| standard | cULus |
|----------|-------|