



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1109A 120-277V, 40A 24HR Timer *Nsi Industries*

| | |
|------------------|--|
| Catalog Number | 1109A |
| Manufacturer | Nsi Industries |
| Description | 24 Hour Time Switch 120-277V SPST Indoor |
| Weight per unit | 2.3 (lbs/each) |
| Product Category | Electromechanical Time Switches |

Features

| | |
|----------------|--------------|
| action | DPST |
| Base | Screw |
| Contact Rating | 120-277 V |
| Number of Pins | 12 Pair |
| Phase | Single Phase |
| Poles | 2 |
| Timing Range | 24 Hour |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | L=4.687 - H=7.937 - W=2.937 |
|------|-----------------------------|

Descriptions

| | |
|------------------------|---|
| Description | 120-277V,40A 24HR TIMER |
| extra long description | TORK 1109A 24 Hour Time Switch 120- |
| Features | 24 hour 120-277V time switch with same day ON/OFF times each day, in NEMA enclosure. DPST contacts. cULus Listed. |
| Long Description | 24 Hour Time Switch 120-277V SPST Indoor |
| Product Type | 24 Hour Time Switch 120-277V SPST Indoor |
| Special Features | SPST 24 Hour Time Switch - Same Day On-Off Times Each Day |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00786261101051 |
| Manufacturers Part Number | 1109A |
| UPC | 786261101051 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | TIMERS |
| Type | 24 Hour Time Switch |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 2.3 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---------------------|
| Application | NSI |
| Enclosure | NEMA 1 Metal Indoor |
| environmental conditions | -40 to 165 F |
| Frequency Rating | 60 Hz |
| Mounting | Screw Mount |
| Operating Temperature | -40 to 165 F |
| standard | cULus |