



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1223I Switch, Hubpro, 3-Way, 20A 120/277V, Iv *Hubbell Wiring Devices*

Catalog Number	1223I
Manufacturer	Hubbell Wiring Devices
Description	Toggle Switch, 3 Poles, 3 Ways, 20 A, 120 to 277 V Ac, SPDT Contact Configuration, Thermoplastic (Body);Nylon (Toggle) Material, Steel Contact Material, Ivory, Back and Side Wired Connection, Screw Mount, Zinc Plated (Bridge), 1.49 In (L) X 1 In (W) X 4.18 In (H), -40 °C Operating Temperature, +75 °C Operating Temperature, 0.2 LB
Weight per unit	0.2000 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	SPDT
amperage rating	20
connection	Back and Side Wired
Contact Rating	Per UL 20
insulation	False
operating cycles	50,000
pallet quantity	4400
Poles	Single Pole
Switch Type	Toggle
Wattage	5540;5540.0000

### Dimensions and Weight

Size	4.18 in x 1.49 in x 1.83 in
------	-----------------------------

### Descriptions

Description	SWITCH, HUBPRO, 3-WAY, 20A 120/277V, IV
extra long description	HWDK 1223I SWITCH, HUBPRO, 3-WAY, 2

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585835327
series	Heavy Duty
UPC	783585835327

### Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	TOGGLE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.2

## Uses, Certifications, and Standards

Enclosure	None
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
standard	UL Listed