



Powering Business Worldwide

1225

Recp Single Surface 30A 125/250V 3P4W BK

UPC: 032664305702

Brand Name: Eaton

Sub Brand: ARROW HART

Type: (1) Toggle Switch, (1) Pilot Light

Special Features: Wiring Type Back and Side Wire, Color White, With Red Lexan Pilot Lens, Neon Lamp

Application: Commercial

Voltage Rating: 120 Vac

Amperage Rating: 15 Amp

Wattage: 25 W (Pilot Light)

Number Of Poles: 1

Contact Configuration: Heavy Duty Brass

Action: Switch

Actuator: Toggle

Connection: Screw

Enclosure: Thermoplastic Top and Backbody are Virtually Unbreakable

Mounting: Mounting Straps Are Zinc Plated to for added corrosion resistance

Size: 1.37 In Width X 0.95 In Depth

Operating Temperature: -20 To 60 Deg C



Powering Business Worldwide

1225

Recp Single Surface 30A 125/250V 3P4W BK

UPC: 032664305702

Brand Name: Eaton

Sub Brand: ARROW HART

Type: (1) Toggle Switch, (1) Pilot Light

Special Features: Wiring Type Back and Side Wire, Color White, With Red Lexan Pilot Lens, Neon Lamp

Application: Commercial

Voltage Rating: 120 Vac

Amperage Rating: 15 Amp

Wattage: 25 W (Pilot Light)

Number Of Poles: 1

Contact Configuration: Heavy Duty Brass

Action: Switch

Actuator: Toggle

Connection: Screw

Enclosure: Thermoplastic Top and Backbody are Virtually Unbreakable

Mounting: Mounting Straps Are Zinc Plated to for added corrosion resistance

Size: 1.37 In Width X 0.95 In Depth

Operating Temperature: -20 To 60 Deg C