



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1225L SW Man Control 20A 120/277V (SPDT) Gy

Pass & Seymour/Legrand

Catalog Number	1225L
Manufacturer	Pass & Seymour/Legrand
Description	Manual Controller Single-Pole, Double-Throw Switch, 20A, 120/277V, Locking.
Weight per unit	0.3030 (lbs/each)
Product Category	Manual Motor Switches & Accy.

Features

amperage rating	20
Contact Configuration	NO
Contact Rating	20Amp, 120/277Vac
insulation	Bare
Poles	1
Voltage Rating	120/277
Wattage	1
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	Locking
Finish	Matte

Dimensions and Weight

Size	3.3"
------	------

Descriptions

Description	SW MAN CONTROL 20A 120/277V (SPDT) GY
extra long description	P&S 1225L SW MAN CONTRL 20A 120/277
Long Description	Manual Controller Single-Pole, Double-Throw Switch, 20A, 120/277V, Locking.
Product Type	SW Man Contrl 20A 120/277V (SPDT) Gy
Special Features	Oversized silver alloy contacts, side wired, can be mounted in standard device box\

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007122527
Manufacturers Part Number	1225-L
UPC	785007122527

Taxonomies, Classifications, and Categories

Category Description	REVERSING
Type	Manual Controller

Trade Size

Amperage	20.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.303

Uses, Certifications, and Standards

Application	Industrial
Enclosure	Box or NEMA 1 sheet steel
Mounting standard	WALL CULUS, UL, CSA, UL listed