

# Eaton 1233-BOX

Catalog Number: 1233-BOX

Eaton power device receptacle, #12 - 4 AWG, 30A, Flush, 125V, Back, Brown, NEMA 5-30R, Two-pole, Three-wire, Two-pole, three-wire, grounding, Screw, Glass-filled nylon, Power, Used with S41



Photo is representative

## General specifications

|                               |                             |
|-------------------------------|-----------------------------|
| <b>Product Name</b>           | <b>Catalog Number</b>       |
| Eaton power device receptacle | 1233-BOX                    |
| <b>UPC</b>                    | <b>Product Length/Depth</b> |
| 032664306204                  | 3.88 in                     |
| <b>Product Height</b>         | <b>Product Width</b>        |
| 2.25 in                       | 2.94 in                     |
| <b>Product Weight</b>         | <b>Compliances</b>          |
| 0.38 lb                       | RoHS Compliant<br>NAFTA     |

**Certifications**  
UL Listed  
NOM  
CSA Certified

## Product specifications

### Used with

S41

### Amperage Rating

30A

### Voltage rating

125 V

### Wiring method

Back

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Color

Brown

### Connection type

Screw

### Style

Power

### Allowable wire size

#12-4 AWG

### NEMA configuration

5-30R

### Torque rating

25 lbf-inch

### Design type

Receptacle

### Material

Glass filled nylon

### Receptacle type

Two-pole, three-wire, grounding

## Resources

### Brochures

[Flush mount receptacles sell sheet](#)

### Catalogs

[Arrow Hart Buyers Guide Section B](#)

### Specifications and datasheets

[Eaton Specification Sheet - 1233-BOX](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)