

# Eaton 1234-BOX

Catalog Number: 1234-BOX

Eaton power device receptacle, #12 - 4 AWG, 30A, Flush, 250V, Back, Black, NEMA 6-30R, Two-pole, Three-wire, Two-pole, three-wire, grounding, Screw, Glass-filled nylon, Power, Used with S42

## General specifications



Photo is representative

### Product Name

Eaton power device receptacle

### Catalog Number

1234-BOX

### UPC

032664306303

### Product Length/Depth

2.25 in

### Product Height

3.88 in

### Product Width

2.38 in

### Product Weight

0.36 lb

### Compliances

RoHS Compliant  
NAFTA

### Certifications

UL Listed  
NOM  
CSA Certified

## defaultTaxonomyAttributeLabel

### Used with

S42

### Amperage Rating

30A

### Voltage rating

250 V

### Wiring method

Back

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Color

Black

### Connection type

Screw

### Style

Power

### Allowable wire size

#12-4 AWG

### NEMA configuration

6-30R

### Torque rating

25 lbf-inch

### Design type

Receptacle

### Material

Glass filled nylon

### Receptacle type

Two-pole, three-wire, grounding

## Resources

### Brochures

[Flush mount receptacles sell sheet](#)

### Catalogs

[Arrow Hart Buyers Guide Section B](#)

### Specifications and datasheets

[Eaton Specification Sheet - 1234-BOX](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)