

## Standard Grade Toggle Switches

Single-Pole, 3-Way, 4-Way  
15A, 120V/AC


### FEATURES

- Industrial design cam action mechanism ensures quiet switch action.
- 3-way switches feature additional push-in common termination for feed-through tapping.
- Unbreakable top and bottom housing eliminates call-backs due to job site breakage.
- Push-in terminals accept #14 AWG solid wire only; side wire terminals accept up to #10 AWG solid wire.
- Long, broad mounting strap virtually eliminates floating installations.
- Patented built-in wire stripper for #12 and #14 AWG wire to speed installation.
- Patented built-in wire looper for pre-looping.
- Tri-combo screws accept Slotted, Phillips, and Robertson-head tools for installation flexibility.
- Lighted models' toggle glows in "off" position.

### Toggle Switches, Non-Grounding

15A 120V/AC; Side Wire & Push Wire

Description	Color Suffix	Catalog No.	
Single-Pole	B, V, W	□ 1301__	•
3-Way	B, V, W	□ 1303__	•


 cULus Listed to UL20, file no. E18704; NOM certified



1303

### Toggle Switches, Grounding

15A 120V/AC; Side Wire & Push Wire

Description	Color Suffix	Catalog No.	
Single-Pole	A, B, LA, V, W	□ 1301-7__	•
3-Way	A, B, LA, V, W	□ 1303-7__	•
4-Way	A, B, LA, V, W	□ 1242-7__	•
Single-Pole, Less Ears	A, B, LA, V, W	□ 1301-73__	•
Lighted, Single-Pole	A, LA, V, W	□ 1301-7LT__	•
Lighted, 3-Way	A, LA, V, W	□ 1303-7LT__	•

 cULus Listed to UL20, file no. E18704; NOM certified. Lighted models also CSA certified to C22.2, no. 111.



1301-7



1301-73

**Color Ordering Information:** For ordering devices, include Cat. No. followed by the color code: A (Almond), B (Brown), LA (Light Almond), V (Ivory), W (White)

**Dimensional Information:** B-60

**Specification Information:** Please visit [www.cooperwiringdevices.com](http://www.cooperwiringdevices.com)

 **NAFTA Compliant:** See page F-21