



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1251RED SW CTR Off Contrl 20A 120/277V (SPDT) RD *Pass & Seymour/Legrand*

Catalog Number	1251RED
Manufacturer	Pass & Seymour/Legrand
Description	20A 120/277V Single Pole Double Throw Manual Controller, Red
Weight per unit	0.2750 (lbs/each)
Product Category	Fan Speed Switches & Controls

### Features

actuator	Toggle
amperage rating	20
connection	Side wire
load	20A
operating cycles	50,000 cycles minimum, resistive, inductive, tungsten filament lamp load (Fed Spec)
Poles	1
Voltage Rating	120/277

### Dimensions and Weight

Size	1.469" Depth x 1.5" Width x 3.281" Height
------	---

### Descriptions

Description	SW CTR OFF CONTRL 20A 120/277V (SPDT) RD
extra long description	P&S 1251RED SW CTR OFF CONTRL 20A 1
Long Description	20A 120/277V Single Pole Double Throw Manual Controller, Red
Product Type	SW CTR Off Contrl 20A 120/277V (SPDT) RD
Special Features	Single Pole, Double Throw Manual Control Switch

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007026283
Manufacturers Part Number	1251RED
UPC	785007026283

### Taxonomies, Classifications, and Categories

Type	Manual Controller
------	-------------------

### Packaging

Carton	1
Package	10
Weight Per each	0.275



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Commercial/Industrial
environmental conditions	UL94 V2
Frequency Rating	60Hz
Mounting	BOX
Operating Temperature	Maximum continuous +75°C, minimum -40°C
standard	RoHS, UL Listed, CSA Listed