

# Conduit Bodies

Threaded and Set Screw Bodies and Kits



Hub Size	Unassembled (body only)			Assembled (with cover and gasket)			Box Quantity	Carton Quantity
	Threaded	Set Screw	Combination	Threaded	Set Screw	Combination		
<b>LR</b>								
½"	11821	1871	13821	12821	12871	14821	10	50
¾"	11822	11872	13822	12822	12872	14822	10	50
1"	11823	11873	13823	12823	12873	14823	5	25
1¼"	11824	11874	13824	12824	12874	14824	—	2
1½"	11825	11875	13825	12825	12875	14825	—	2
2"	11826	11876	13826	12826	12876	14826	—	1
2½"				12827			—	1
3"				12828			—	1
3½"				12829			—	1
4"				12830			—	1
<b>C</b>								
½"	11831	11881	13831	12831	12881	14831	10	50
¾"	11832	11882	13832	12832	12882	14832	10	50
1"	11833	11883	13833	12833	12883	14833	5	25
1¼"	11834	11884	13834	12834	12884	14834	—	2
1½"	11835	11885	13835	12835	12885	14835	—	2
2"	11836	11886	13836	12836	12886	14836	—	1
2½"				12837			—	1
3"				12838			—	1
<b>T</b>								
½"	11841	11891	13841	12841	12891	14841	10	50
¾"	11842	11892	13842	12842	12892	14842	10	50
1"	11843	11893	13843	12843	12893	14843	5	25
1¼"	11844	11894	13844	12844	12894	14844	—	2
1½"	11845	11895	13845	12845	12895	14845	—	2
2"	11846	11896	13846	12846	12896	14846	—	1
2½"				12847			—	1
3"				12848			—	1

CONDUIT BODIES AND COVERS

# Conduit Bodies

Threaded and Set Screw Bodies and Kits



Hub Size	Unassembled (body only) Catalog No.			Assembled (with cover and gasket) Catalog No.			Box Quantity	Carton Quantity
	Threaded	Set Screw	Combination	Threaded	Set Screw	Combination		
<b>LR</b>								
½"	11821	1871	13821	12821	12871	14821	10	50
¾"	11822	11872	13822	12822	12872	14822	10	50
1"	11823	11873	13823	12823	12873	14823	5	25
1¼"	11824	11874	13824	12824	12874	14824	—	2
1½"	11825	11875	13825	12825	12875	14825	—	2
2"	11826	11876	13826	12826	12876	14826	—	1
2½"				12827			—	1
3"				12828			—	1
3½"				12829			—	1
4"				12830			—	1
<b>C</b>								
½"	11831	11881	13831	12831	12881	14831	10	50
¾"	11832	11882	13832	12832	12882	14832	10	50
1"	11833	11883	13833	12833	12883	14833	5	25
1¼"	11834	11884	13834	12834	12884	14834	—	2
1½"	11835	11885	13835	12835	12885	14835	—	2
2"	11836	11886	13836	12836	12886	14836	—	1
2½"				12837			—	1
3"				12838			—	1
<b>T</b>								
½"	11841	11891	13841	12841	12891	14841	10	50
¾"	11842	11892	13842	12842	12892	14842	10	50
1"	11843	11893	13843	12843	12893	14843	5	25
1¼"	11844	11894	13844	12844	12894	14844	—	2
1½"	11845	11895	13845	12845	12895	14845	—	2
2"	11846	11896	13846	12846	12896	14846	—	1
2½"				12847			—	1
3"				12848			—	1

CONDUIT BODIES AND COVERS