



Part Number	Size	T Min.	OD	ID Min.	E	B	D Min.	L Min.
A52AE12	$\frac{1}{2}$ "	0.109"	0.840"	0.578"	0.852"	0.836"	1.500"	120"
A52AG12	$\frac{3}{4}$ "	0.113"	1.050"	0.780"	1.064"	1.046"	1.750"	120"
A52BA12	1"	0.133"	1.315"	1.004"	1.330"	1.310"	2.000"	120"
A52BC12	1 $\frac{1}{4}$ "	0.140"	1.660"	1.335"	1.667"	1.655"	2.250"	120"
A52BE12	1 $\frac{1}{2}$ "	0.145"	1.900"	1.564"	1.918"	1.894"	2.500"	120"
A52CA12	2"	0.154"	2.375"	2.021"	2.393"	2.369"	3.000"	120"
A52CE12	2 $\frac{1}{2}$ "	0.203"	2.875"	2.414"	2.890"	2.868"	3.250"	120"
A52DA12	3"	0.216"	3.500"	3.008"	3.515"	3.492"	3.750"	120"
A52DE12	3 $\frac{1}{2}$ "	0.226"	4.000"	3.486"	4.015"	3.992"	4.000"	120"
A52EA12	4"	0.237"	4.500"	3.961"	4.515"	4.491"	4.500"	120"
A52FA12	5"	0.258"	5.563"	4.975"	5.593"	5.553"	5.500"	120"
A52GA12	6"	0.280"	6.625"	5.986"	6.658"	6.614"	6.125"	120"
A52JA12	8"	0.322"	8.625"	7.853"	8.670"	8.610"	6.375"	120"

Dimensions are Nominal

ETL Listed
 Conforms to UL-651
 NEMA TC2 Compliant
 See NEC Article 352 for use
 Sunlight Resistant
 Max 90° C Wire



2" & greater are CSA Listed.



CANTEX
 INC.
 Fort Worth, TEXAS

Schedule 40 10' Rigid PVC Conduit

Drawn By: D. Gwinn | Date: 8/21/26 | Ref. A52AE12