

# Specifications

## Eaton 14002-2

Eaton Bussmann series power terminal block, 600 Vac, 600 Vdc, 115 A, Two-pole, SCCR: 10 kA



### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series power terminal block
<b>CATALOG NUMBER</b>	14002-2
<b>UPC</b>	051712206990
<b>EAN</b>	5027590508063
<b>PRODUCT LENGTH/DEPTH</b>	0.5 in
<b>PRODUCT HEIGHT</b>	0.5 in
<b>PRODUCT WIDTH</b>	0.5 in
<b>PRODUCT WEIGHT</b>	0.034 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	Contact factory RoHS Compliant
<b>CERTIFICATIONS</b>	Contact Manufacturer



Powering Business Worldwide

## Electrical rating

AMPERAGE RATING	115A
SHORT-CIRCUIT RATING	SCCR: 10 kAIC
VOLTAGE RATING	600 Vac, 600 Vdc

## Physical details

NUMBER OF POLES	Two-pole
TYPE	Power terminal block

## Resources

[14002-2~#80K \(3 WKS\)](#)

### CATALOGS

[Bussmann series full line catalog 1007, section 09 - power distribution blocks](#)

[Bussmann series complete full line catalog no. 1007](#)

### MULTIMEDIA

[Bussmann series Fuseology](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - 14002-2](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton 14002-2

Eaton Bussmann series power terminal block, 600 Vac, 600 Vdc, 115 A, Two-pole, SCCR: 10 kA



### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series power terminal block
<b>CATALOG NUMBER</b>	14002-2
<b>UPC</b>	051712206990
<b>EAN</b>	5027590508063
<b>PRODUCT LENGTH/DEPTH</b>	0.5 in
<b>PRODUCT HEIGHT</b>	0.5 in
<b>PRODUCT WIDTH</b>	0.5 in
<b>PRODUCT WEIGHT</b>	0.034 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	Contact factory RoHS Compliant
<b>CERTIFICATIONS</b>	Contact Manufacturer



*Powering Business Worldwide*

## Electrical rating

AMPERAGE RATING	115A
SHORT-CIRCUIT RATING	SCCR: 10 kAIC
VOLTAGE RATING	600 Vac, 600 Vdc

## Physical details

NUMBER OF POLES	Two-pole
TYPE	Power terminal block

## Resources

[14002-2~#80K \(3 WKS\)](#)

### CATALOGS

[Bussmann series full line catalog 1007, section 09 - power distribution blocks](#)

[Bussmann series complete full line catalog no. 1007](#)

### MULTIMEDIA

[Bussmann series Fuseology](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - 14002-2](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

