



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 1433 Plug Ins 20A 125V 2P3W STR YI *Eaton Wiring Devices*

Catalog Number	1433
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Severe Duty Straight Blade Plug, #14-8 Awg, 20A, Industrial, 125V, Back Wire, Yellow, Black, Nickel-Plated Brass, Corrosion Resistant, Nylon, 5-20P, Two Pole, Three Wire, Grounding, Screw, 0.38-1" In Diameter, Thermoplastic, Core Pack
Weight per unit	N/A
Product Category	Plugs, Connectors, Inlets, Out

### Features

dimensions	1.6900 IN X 1.6900 IN X 1.7500 IN
Material	Thermoplastic
media	Yes

### Descriptions

Description	PLUG INS 20A 125V 2P3W STR YL
extra long description	EWD 1433 Plug Ins 20A 125V 2P3W Str
Features	Severe duty devices offer superior materials and design to provide excellent insulation and durability in complex industrial environments.
Long Description	Eaton Arrow Hart severe duty straight blade plug,#14-8 AWG,20A,Industrial,125V,Back wire,Yellow,black,Nickel-plated brass,Corrosion Resistant,Nylon,5-20P,Two pole,three wire,grounding,Screw,0.38-1" in diameter,Thermoplastic,Core pack
Product Type	Plug Ins 20A 125V 2P3W STR YI
Special Features	Insulated straight blade

### Manufacturer Information

Brand	Eaton
GTIN	00040893630830
Manufacturers Part Number	1433
UPC	040893630830

### Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Severe duty

### Packaging

Carton	1
Package	10
Weight Per each	0



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application .....	Ind Facilities & Factories - Industrial Facilities/Factories - Other .....
environmental conditions .....	Corrosive .....
standard .....	cULus Listed .....