
20A, 125V RUBBER DUST-TIGHT PLUG, YELLOW

1433P | [Pass & Seymour](#)



FEATURES & BENEFITS

Straight Blade Rubber Plug 20amp 125volt 5-20p

- Rubber body construction stands up to impacts, oils, chemicals, heat, and weather.
- Floating blades allow self-alignment with contacts for a firm, even electrical connection.
- Terminal screws backed-out, ready-to-wire, saving time and money.
- Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.
- Quick-drive assembly screws allow for fast installation, saving time and money.
- Self-centering cord clamps provide superior strain relief.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Yellow

Number Of Poles: 2

Number Of Wires: 3

Special Features: Rubber, Dust-Tight

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: c22.2 No. 42M

CSA Standard: Yes

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121402

UR: No

DIMENSIONS

Depth (US): 2.59"

Diameter (US): 1.60"

Height (US): 1.93"
Length (US): 2.44"

TECHNICAL INFORMATION

Amps: 20A
NEMA Configuration Number: 5-20
Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant



20A, 125V RUBBER DUST-TIGHT PLUG, YELLOW

1433P | [Pass & Seymour](#)



FEATURES & BENEFITS

Straight Blade Rubber Plug 20amp 125volt 5-20p

- Rubber body construction stands up to impacts, oils, chemicals, heat, and weather.
- Floating blades allow self-alignment with contacts for a firm, even electrical connection.
- Terminal screws backed-out, ready-to-wire, saving time and money.
- Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.
- Quick-drive assembly screws allow for fast installation, saving time and money.
- Self-centering cord clamps provide superior strain relief.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Yellow

Number Of Poles: 2

Number Of Wires: 3

Special Features: Rubber, Dust-Tight

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: c22.2 No. 42M

CSA Standard: Yes

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121402

UR: No

DIMENSIONS

Depth (US): 2.59"

Diameter (US): 1.60"

Height (US): 1.93"
Length (US): 2.44"

TECHNICAL INFORMATION

Amps: 20A
NEMA Configuration Number: 5-20
Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

